



- 1: Coaxial out
- 2: Optical Out
- 3: USB-C input
- 4: USB-B input
- 5: Power indicator

**IMPORTANT NOTICE:**

- 1: Please use the correct corresponding OTG data cable
- 2: The input USB ports can not be used at the same time - doing so will cause malfunction or possible damage.



**Parameter:**

Support Format (max) .....	DSD128
Sampling Rate (USB decode) .....	192kHz/24bit
Sampling Rate (Optical/Coaxial) .....	192kHz/24bit
Frequency Response .....	20Hz~40kHz
Signal to Noise Ratio .....	>117dB
Harmonic Distortion .....	<0.002%
Input .....	Type-C input×1/USB input×1
Output .....	Optical output×1/Coaxial output×1